

Chemieprene <u>THERMOPLASTIC ELASTOMER</u>

Injection Moulding Processing Guide for Chemieprene TPE ES series

Processing Temperature		
Temperatures	VALUE(Metic)	
1st Zone-Rear	165-175 °C	
2nd Zone-Center	170-185 ℃	
3rd Zone-Front	180-190 °C	
4th Zone-Nozzle	175-185 ℃	
Mold Temperature	40-50 °℃	
Pressure, Velocity, Recovery, Timers		
Pressure	VALUE(Metic)	
1st Stage-Boost	$50-100 \text{ kg/cm}^2$	
2nd Stage-Hold	25-50 % of Boost	
Back Pressure	$5-10 \text{ kg/cm}^2$	
Velocity		
Injection Velocity	Fast 30-80 mm/sec	
Recovery		
Screw Speed	75-125 RPM	
Timers		
Hold Time(Thick part)	4-10 sec	
Hold Time(Thin part)	1-3 sec	
Drying		
Drying Temperature	60-70°ℂ	
Drying Time	2-3 hrs	
Purging		

Purging

Purge thoroughly before and after use of this product with a low flow (0.5-3 MFR) polypropylene(PP) or polyethylene(PE)

Coloring

Color concentrates with polypropylene (PP), ethylene Vinyl acetate (EVA), or low density polyethylene (LDPE) Carries are most suitable for coloring, concentrates based on PVC should not be used. The final determination of color concentrate be determined by the customer.

Regrind

Regrind levels up to 20% can be used with minimal property loss, provided that the regrind is free of contamination.

CP Chemie Resources (Malaysia) Sdn Bhd

URL: www.cpchemie.com Email: info@cpchemie.com

All Information supplied by or on behalf of CP Chemie Resources (M) Sdn Bhd in relationship to its product, whether in nature of data, recommendations or otherwise, is supported by research and believed reliable, but the Company assume no liability whatsoever in respect of application, processing or use made of the aforementioned information and products, or any consequence thereof. This data provided shall not absolve the customer of the responsibility to make test for his intended purpose or process. Therefore, the Company makes no warranties and assumes no liability in connection with any use of this data.